

Cut your cores in an efficiently and relaxed way

BM M10



- Core-ID: 25.4-152.4 mm
- Wall thickness: max. 11 mm (plastic) / 20 mm (cardboard)
- Core length up to: 3,000 mm
- Cut: manual, for single cuts and small quantities
- Knife: free running crush cut knife

BM M10-PS



- Core-ID: 25.4-152.4 mm
- Wall thickness: max. 11 mm (plastic) / 20 mm (cardboard)
- Core length up to: 3,000 mm
- Cut: pneumatic, for single cuts and small quantities
- Knife: free running crush cut knife

BM HA25



- Core-ID: 25.4-152.4 mm
- Wall thickness: max. 11 mm (plastic) / 20 mm (cardboard)
- Core length up to: 2,000 mm
- Cut: automatic, for medium volume use for all cases
- Knife: free running crush cut knife

BM HA35



- Core-ID: 12.7-152.4 mm
- Wall thickness: max. 11 mm (plastic) / 20 mm (cardboard)
- Core length up to: 4,000 mm
- Cut: automatic, for medium to high volume user
- Knife: free running crush cut knife
- Optional: automatic parent core injector system, section separation system etc.

BM HA40



- Core-ID: 12.7-152.4 mm
- Wall thickness: max. 11 mm (plastic) / 20 mm (cardboard)
- Core length up to: 4,000 mm
- Cut: automatic, for medium to high volume user
- Knife: crush cut knife
- Optional: automatic parent core injector system, section separation system etc.

BM HA45



- Core-ID: 76.2-304.8 mm
- Wall thickness: max. 11 mm (plastic) / 20 mm (cardboard)
- Core length up to: 4,000 mm
- Cut: automatic, for medium to high volume user
- Knife: free running crush cut knife
- Optional: Foot actuation